[Hi-Block Containers]

Container dimensions

Combination

⊠CONTACT
ECONTACT

Product number	Capacity (mL)	Diameter (mm)	Body diameter (mm)	Set height (mm)	Inside diameter (mm)	Materials
No.30	About 33	53.5	42.2	57.0	39.5	Body : HDPE Cap : HDPE Inner lid : HDPE

Body	Сар	Inner lid	Notes	Product image	
Quantity	Quantity	Quantity			
BBL-30	CBL-30	SBL-30F	The body, cap, and inner lid of this container are packed	7 1	
100	100	100	together as a set.		

- •To use this container safely and effectively, use all parts (body, cap, and inner lid) as a set.
- ·If you use this product without the original cap or inner lid, liquid leakage can occur.
- •Torque the cap to 100 cN·m or more when using this product.
- •Please note that some items may run out of stock.
- ·Coloring service is available depending on the lot size.
- ·Standard colors are natural color and black. Both colors are in stock.
- ·Please note that when the mold is renewed or updated, dimensions and other specifications may change to some degree.
- ·Air tightness of this product, you may vary depending on content, please review prior to use in the sample. For more information, please contact us.
- •Contact our sales desk before using this product in a mixing machine.




An anti-backspin ratchet is employed to prevent the cap from being closed incompletely or loosened when the container is kept in a refrigerator.




Easy-to-hold inner lid



Surface with emboss processing, which is writable with oil-based pens. You can use label stickers.



You can stir the container with ingredients in a mixing machine. For required attachments, contact the manufacturer of your machine.



Even when you pile up Hi-Block containers, they will not topple due to the impact of closing the refrigerator door strongly.

