


【Hi-Smart Containers】

Container dimensions

Product number	Capacity (mL)	Diameter (mm)	Set height (mm)	Body flange dia. (mm)	Cap dia. (incl. hinge) (mm)	Materials
No.300	About 330	66.5	About 99.2	93.1	95.4 *Reference	Body : HDPE Cap : PP

Combination

✉ CONTACT

Body	Cap	Notes	Product image
Quantity	Quantity		
BSM-300	CSM-300P	-	
300	600		

- Please note that some items may run out of stock.
- Coloring service is available depending on the lot size.
- Standard colors are natural color and black.Both colors are in stock.
- Please note that when the mold is renewed or updated, dimensions and other specifications may change somewhat.
- Air tightness of this product may vary depending on the contents. Please test it on a sample prior to use. For more information, please contact us.



Tear off the tamper evident strip around the cap in the direction of the arrow to remove the cap.



Both container bodies and caps can be nested. This helps save storage space considerably.



When using Hi-Smart Container, contents that stick to the back of the cap can be rubbed off.



Hi-Smart Container can be recapped even after the tamper evident strip is torn off.